

The ideal balance of child-resistant and senior friendly packaging designed for nasal and ophthalmic products.

- Proven two-piece push and turn technology patented by Comar
- Meets CPSC protocol for child-resistant package testing
- Manufactured in facilities that comply with cGMP and ISO standards



SecureCapTM
CHILD-RESISTANT CLOSURES

SecureCap™

CHILD-RESISTANT CLOSURES



Reduce the risk of accidental ingestion or exposure

The SecureCap™ design is significantly difficult for children under 5 years old to open, but not too difficult for an average adult to open. Designed to mimic existing closure system, no downward force

is required to engage inner and outer components during application of the closure to the bottle, making it much more adult friendly.

Meets CPSC and USP Standards

SecureCap™ closures passed the Consumer Product Safety Commission (CPSC) test protocol for child-resistant closures, and met USP standards for performance and quality.

- CPSC Protocol Title 16 of the Code of Federal Regulations (CFR) 1700.2
- USP 27 <661> Extractable Testing
- USP 27 <661> Light Transmission Testing
- USP 32 <671> Container Performance Testing for moisture vapor transmission rates (MVTR)

A ready-made solution for your product

SecureCap™ 15mm Child-Resistant Closures are ideal for OTC or prescription ophthalmic and nasal products that contain 0.08mg. or more of an imidazoline.

The closures are available individually and can be combined with Comar bottles and dropper tips for a complete packaging solution.

Part No.	Description	Parts/Box
14-0949	SecureCap™ 15mm CR closure (15-415) unlined, non-sterile	3,000
12-0008-014	Bottle, 15mL, white, LDPE	1,100
12-0347-002	Bottle, 10mL, white, LDPE	1,400
22-0615	Dropper Tip	18,000

SecureCap™ Additional Benefits

- Experience has shown that the closure can be applied utilizing existing capping equipment on the filling line, resulting in reduced costs and time to transition to a new closure when compared to other alternatives
- The closures accommodate industry-standard bottle finishes, and are also available in custom sizes and configurations
- In many cases, the design allows for the use of existing materials, minimizing the need for packaging stability testing
- Customizable inner closure is adjustable to accommodate critical tip and shoulder dimensions (with tooling)
- Manufactured in the USA

Comar LLC
One Comar Place
Buena, NJ 08310
1.856.507.5409
www.comar.com/securecap

